



Ultra flexible, offline, multi-platform selective soldering system













JADE PRO

Ultra flexible, offline, multi-platform selective soldering system



Designed to meet the needs of the small batch manufacturer who requires high levels of production flexibility. The Jade PRO offers the ability to regularly change solder alloys without incurring expensive down time, whilst the solder bath cools down and heats up during a regular manual changeover process.

The Jade PRO is a hand load system, incorporating a universally adjustable tooling carrier capable of accommodating PCBs or pallets up to 457x508mm. In its basic format, the Jade PRO is configured with a single solder bath. In the Jade PRO Duplex guise, the machine can be configured with twin adjacent solder baths on independent Z axis drives. This achieves increased production flexibility by permitting use of two different nozzle tip sizes which can be allocated as process requirements dictate within any particular area on a PCB.

All of the above Jade PRO configurations can be offered with optional automatic heated solder bath change stations. Using this system the non-operational solder bath and pump system is stationed at one of two heated park positions located at either side of the main machine. This heated station maintains the correct solder temperature within the bath that is idle, so that when changeover occurs, the replacement bath can resume immediate production. A single automatic solder bath change station is identified as a PLUS configuration, whilst twin stations (located at both sides of the machine) are identified as PLUS PLUS configurations. On this basis Duplex machines with the PLUS PLUS identity will operate with 4 individual solder bath and pump systems.



NITROGEN PURITY ANALYSER



FLUX HEAD



MULTI-DIP NOZZLE



DUPLEX TWIN SOLDER BATH ARRANGEMENT

Solder bath and pump assemblies with twin Drop-Jet flux head and programming camera.



OPERATION

The Jade PRO series is controlled by a PC, through PillarCOMM, a Windows® based 'Point & Click' interface with a PCB image display. Additionally our PillarPAD offline programming package allows the operator to produce programs independently from the machine using Gerber data.

SOLDER BATH REMOVAL/ REPLACEMENT TROLLEY









PRO PLUS SIDE MOUNTED AUTO BATH CHANGEOVER

Solder baths are individually tagged so that incorrect solder alloys cannot be selected with respect to any specific customer generated program. The operational solder bath(s) has its own allocated solder feeder which is also tagged in order to prevent incorrect solder alloy top up.

STANDARD FEATURES

DC servo drives

Integral PC and machine mounted TFT monitor

Inerted Nitrogen system

Auto motorised wire solder feed & level detect

Solder bath coding - identifies correct bath for program

Drop-Jet fluxer

Manual fiducial correction system

Solder wave height measurement and correction

Process viewing camera(s)

Multilevel password protection

Light stack

Six AP style solder nozzle tips

Internal fume extraction

Colour programming camera

PillarPAD offline programming system

Universally adjustable tooling carrier

Thermal nozzle calibration system using integrated setting camera - requires manual correction

PillarCOMM Windows® based 'Point & Click' interface

Lead-free compatible

Day-to-day service kit

MONITORING OPTIONS

Flux presence sensor - thermistor style

Flux spray, flow and spray & flow

Pump rpm

 O_2 ppm

Nitrogen flow

SYSTEM OPTIONS

Side mounted auto bath changeover - PLUS configuration

Top-side instant IR preheat

Bottom-side slide in / out instant IR preheat

Closed loop pyrometer temperature control

Bottom-side hot Nitrogen selective preheat

Automatic fiducial correction

Ultrasonic fluxing

Dual Drop-Jet / ultrasonic fluxing

Laser PCB warp correction

Twin solder bath capability on independent Z axis

Micro nozzle assembly

Large solder bath for dedicated single dip applications

Solder bath removal trolley

Solder reel identification

Larger PCB handling size

PILLARGEN-40/80 NITROGEN GENERATOR



Pillarhouse... Expect innovation

www.pillarhouse.co.uk





SPECIFICATIONS

Height: 1230mm / 48" to 2025mm / 80"- with light stack

Width: 1250mm / 49" to 1700mm / 67"- with side auto-changer

Depth: 1495mm / 59"

1720mm / 68" with flux bottles

Board size: 457mm x 508mm / 18"x 20"

Edge clearance: Above / below 3mm

Height clearance: Above / below 40mm nominal

90mm max. top-side only

Solder: Most commonly used solder types - including lead-free

Solder pot capacity: 20kg standard - 30kg large bath Applicators: AP style - 2.5mm to 16mm dia.

Extended AP style - 2.5mm to 20mm dia.

Micro nozzle - 1.5mm to 2.5mm Jet-Tip style - 6mm to 40mm dia. Jet-Wave style - up to 25mm width

Special dedicated nozzles available upon request Low maintenance Drop-Jet system. Low solids

(below 8%), no clean flux, pressurised and inerted

system, optional water-soluble system available

X, Y & Z axis resolution: 0.1mm

Repeatability: +/- 0.05mm

Flux:

Nitrogen usage: Up to 40 litres gas/min per bath using single bath with

standard AP solder nozzle, 5 bar pressure Up to 80 litres gas/min using Duplex twin bath

configuration. Refer to Pillarhouse for Nitrogen usage requirement with dedicated multi-tube nozzle assemblies

Nitrogen purity: 99.995% or better
Air supply pressure: 5 bar / 72 psi

Power supplies: Three-phase + neutral + PE

Voltage: 230V phase to neutral / 400V phase to phase

Frequency: 50/60Hz

Power: Maximum 9kVA per phase


- machine configuration dependent


Transport: Hand load

Tooling: Integral adjustable board guides, includes finger

extensions and board clamps

Programming: PillarCOMM Windows® based 'Point & Click' interface





Pillarhouse International Ltd.

Rodney Way, Widford, Chelmsford, Essex CM1 3BY UK Pillarhouse USA, Inc.

201 Lively Blvd, Elk Grove Village, IL 60007 USA Pillarhouse (Suzhou) Soldering Systems Co., Ltd. 11 Yuangi Road, Xiangcheng, Suzhou, China 215131 www.pillarhouse.co.uk

Tel: +44 (0) 1245 491333 Fax: +44 (0) 1245 491331

www.pillarhouseusa.com

Tel: +1 847 593 9080 Fax: +1 847 593 9084

www.pillarhouse.cn

Tel: +86 512 6586 0460 Fax: +86 512 6959 0567